

P-FIX - Feed-through connector



3038956

<https://www.phoenixcontact.com/us/products/3038956>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Feed-through connector, width: 4 mm, height: 10.5 mm, color: gray



Your advantages

- Can be used in all ...-TG disconnect terminal blocks from the CLIPLINE complete system
- The P-FIX contact metal seals the disconnect point with the same shape and cannot be removed again once fitted

Commercial data

Item number	3038956
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4017918975289
Weight per piece (including packing)	0.472 g
Weight per piece (excluding packing)	0.45 g
Customs tariff number	85389099
Country of origin	PL

P-FIX - Feed-through connector



3038956

<https://www.phoenixcontact.com/us/products/3038956>

Technical data

Product properties

Product type	Bridge
--------------	--------

Connection data

Maximum load current	20 A
----------------------	------

Dimensions

Width	4 mm
Height	10.5 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-40 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

P-FIX - Feed-through connector

3038956

<https://www.phoenixcontact.com/us/products/3038956>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3038956>

 CSA Approval ID: 2030668				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	-	15 A	-	-

P-FIX - Feed-through connector



3038956

<https://www.phoenixcontact.com/us/products/3038956>

Classifications

ECLASS

ECLASS-13.0	27141192
ECLASS-15.0	27141192

ETIM

ETIM 9.0	EC004592
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

P-FIX - Feed-through connector



3038956
<https://www.phoenixcontact.com/us/products/3038956>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com