

FTP-3/17S - Test plug

3069985

<https://www.phoenixcontact.com/us/products/3069985>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Test plug, number of positions: 17, color: gray



Your advantages

- Easy and time saving, thanks to functional grouping of switching operations
- Cost-effective, thanks to the tailored, modular design and use of standardized CLIPLINE complete accessories
- Space saving, thanks to offset test socket arrangement
- Maximum safety with leading and automatic transformer short circuit
- The automatically generated transformer short circuit and the shock-proof design ensure the highest degree of safety during measurement

- The integrated, robust switch contact is designed for the most stringent demands, and the use of high-quality materials ensures the transmission of signal currents, even after multiple actuations

Commercial data

Item number	3069985
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626396095
Weight per piece (including packing)	754.93 g
Weight per piece (excluding packing)	618.56 g
Customs tariff number	85366990
Country of origin	PL

FTP-3/17S - Test plug

3069985

<https://www.phoenixcontact.com/us/products/3069985>



Technical data


Product properties

Product type	Test plug terminal block
Number of positions	17
Pitch	8.2 mm
Potentials	17

Connection data

Test socket torque	0.5
--------------------	-----

Dimensions

Dimensional drawing	
	
Width	164.3 mm
Height	86 mm
Pitch	8.2 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FTP-3/17S - Test plug


3069985

<https://www.phoenixcontact.com/us/products/3069985>




Drawings

Dimensional drawing



Circuit diagram



FTP-3/17S - Test plug

3069985

<https://www.phoenixcontact.com/us/products/3069985>



Classifications

ECLASS

ECLASS-13.0	27440313
-------------	----------

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

FTP-3/17S - Test plug

3069985

<https://www.phoenixcontact.com/us/products/3069985>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com