

# AI 50 -25 BU - Ferrule

3200726

<https://www.phoenixcontact.com/us/products/3200726>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 25 mm, sleeve length: 40 mm, color: blue

## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3200726       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 25 pc         |
| Sales key                            | BH34          |
| Product key                          | BH3411        |
| GTIN                                 | 4017918094317 |
| Weight per piece (including packing) | 3.4 g         |
| Weight per piece (excluding packing) | 3.32 g        |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

## Technical data

### Product properties


|                    |                                                                            |
|--------------------|----------------------------------------------------------------------------|
| Product type       | Cable end sleeve                                                           |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M                            |
| Product property   | UL certified                                                               |
|                    | Made from soft tin-plated electrolytic copper                              |
|                    | Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size |
|                    | Plastic collar made of polypropylene                                       |
|                    | Halogen-free                                                               |
|                    | Long/short-term temperature: +105°C/+120°C                                 |

### Connection data

#### Conductor connection

|                                       |                    |
|---------------------------------------|--------------------|
| Conductor cross-section flexible max. | 50 mm <sup>2</sup> |
| Conductor cross-section AWG max.      | 1/0                |
| Stripping length                      | 30 mm              |

### Dimensions

|                                           |                                                                                      |
|-------------------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing                       |  |
| Sleeve length                             | 40 mm                                                                                |
| Length contact range                      | 25 mm                                                                                |
| Maximum stripping length                  | 30 mm                                                                                |
| Ferrule diameter                          | 10.3 mm                                                                              |
| Sleeve wall thickness                     | 0.35 mm                                                                              |
| Insulating collar thickness               | 0.6 mm                                                                               |
| Inner dimensions of the insulating collar | 15 mm                                                                                |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | blue (RAL 5015)                |
| Material                               | CU-DHP                         |
| Flammability rating according to UL 94 | HB                             |
| Coating                                | galvanically tin-plated        |
| Surface characteristics                | Tin-plated                     |
| Components                             | free from silicone and halogen |

### Mechanical properties

#### Technical data

# AI 50 -25 BU - Ferrule

3200726

<https://www.phoenixcontact.com/us/products/3200726>



|               |       |
|---------------|-------|
| Sleeve length | 40 mm |
|---------------|-------|

## Environmental and real-life conditions

### Ambient conditions


|                        |                                             |
|------------------------|---------------------------------------------|
| Permanent temperature  | 105 °C (-40 °C no load / 0 °C dynamic load) |
| Short-term temperature | 120 °C                                      |

## Standards and regulations

|                              |                                    |
|------------------------------|------------------------------------|
| Design according to standard | DIN 46228-4, UL 486F-E, NFC 63-023 |
|------------------------------|------------------------------------|

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI 50 -25 BU - Ferrule

3200726

<https://www.phoenixcontact.com/us/products/3200726>



## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3200726>



**cULus Listed**

Approval ID: E488001

# AI 50 -25 BU - Ferrule

3200726

<https://www.phoenixcontact.com/us/products/3200726>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000005 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

# AI 50 -25 BU - Ferrule



3200726  
<https://www.phoenixcontact.com/us/products/3200726>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)