

CD COVER 80 BU - Cover profile

3240334

<https://www.phoenixcontact.com/us/products/3240334>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, blue, width: 80 mm, length: 2000 mm

Commercial data

Item number	3240334
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE74
Product key	BE7432
GTIN	4046356508148
Weight per piece (including packing)	556 g
Weight per piece (excluding packing)	434 g
Customs tariff number	39259020
Country of origin	DE

CD COVER 80 BU - Cover profile

3240334

<https://www.phoenixcontact.com/us/products/3240334>



Technical data

Product properties

Product type	Cover
--------------	-------

Dimensions

Width	80 mm
Height	2000 mm
Depth	11 mm
Length	2000 mm

Material specifications

Color	blue (RAL 5015)
Material	PVC
Flammability rating according to UL 94	V0
Components	Lead-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

CD COVER 80 BU - Cover profile



3240334

<https://www.phoenixcontact.com/us/products/3240334>

Classifications

ECLASS

ECLASS-13.0	27400776
ECLASS-15.0	27400776

ETIM

ETIM 9.0	EC000727
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD COVER 80 BU - Cover profile



3240334

<https://www.phoenixcontact.com/us/products/3240334>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com