


CD-HF COVER 80 - Cover profile

3240373

<https://www.phoenixcontact.com/us/products/3240373>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, light gray, halogen-free, width: 80 mm, length: 2000 mm

Commercial data

Item number	3240373
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE74
Product key	BE7441
GTIN	4046356508582
Weight per piece (including packing)	456 g
Weight per piece (excluding packing)	334 g
Customs tariff number	39259020
Country of origin	DE

CD-HF COVER 80 - Cover profile

3240373

<https://www.phoenixcontact.com/us/products/3240373>



Technical data

Product properties

Product type	Cover
--------------	-------

Dimensions

Width	80 mm
Height	2000 mm
Depth	11 mm
Length	2000 mm

Material specifications

Color	light gray (RAL 7035)
Material	PC/ABS
Flammability rating according to UL 94	V0
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD-HF COVER 80 - Cover profile



3240373

<https://www.phoenixcontact.com/us/products/3240373>

Classifications

ECLASS

ECLASS-13.0	27400776
ECLASS-15.0	27400776

ETIM

ETIM 9.0	EC000727
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD-HF COVER 80 - Cover profile

3240373

<https://www.phoenixcontact.com/us/products/3240373>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com