

WP-GR HF CTA M40 BK - Protective hose screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corrugated pipe adapter, with internal thread, for connecting corrugated pipes to HEAVYCON EVO M40 plastic cable glands or ADVANCE M40 plastic housings, straight, black, IP66.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3241223 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356860857 |
| Weight per piece (including packing) | 41.38 g |
| Weight per piece (excluding packing) | 41.38 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

WP-GR HF CTA M40 BK - Protective hose screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Technical data

Product properties

| | |
|--------------|----------------------------------|
| Product type | Protective hose screw connection |
| Application | Cable gland |
| Thread type | metric |

Material specifications

| | |
|--|--|
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Material for screw connection | PA |
| Components | free from silicone, halogen, and cadmium |

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Ambient temperature (operation) | -40 °C ... 115 °C |

Mounting

| | |
|---------------|--|
| Assembly note | The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used. |
|---------------|--|

WP-GR HF CTA M40 BK - Protective hose screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27430311 |
| ECLASS-15.0 | 27430311 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001178 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

WP-GR HF CTA M40 BK - Protective hose screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.0 Climate Change

| | |
|---------|---------------|
| CO2e kg | 3.865 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com