


## ALF70C471DF450

ALF70, Aluminum Electrolytic, 470 uF, 20%, 450 VDC, -40/+85°C, 22.5 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                     |
|--------------------------|-------------------------------------|
| Series                   | ALF70                               |
| Dielectric               | Aluminum Electrolytic               |
| Style                    | Press-Fit                           |
| Description              | Aluminum Electrolytic               |
| RoHS                     | Yes                                 |
| Lead                     | 4 Pin Press-Fit                     |
| Halogen Free             | Yes                                 |
| Typical Component Weight | 80 g                                |
| Notes                    | Dimensions D And L Include Slewing. |
| Shelf Life               | 156 Weeks                           |

### Dimensions

|    |                    |
|----|--------------------|
| D  | 35mm +1mm          |
| L  | 50mm +/-2mm        |
| S  | 22.5mm +/-0.1mm    |
| LL | 5.5mm +/-1mm       |
| F  | 1.486mm +/-0.076mm |

### Packaging Specifications

|           |      |
|-----------|------|
| Slewing   | Yes  |
| Packaging | Bulk |

### Specifications

|                   |                                                                                       |
|-------------------|---------------------------------------------------------------------------------------|
| Capacitance       | 470 uF                                                                                |
| Tolerance         | 20%                                                                                   |
| Voltage DC        | 450 VDC, 495 VDC (Surge)                                                              |
| Temperature Range | -40/+85°C                                                                             |
| Rated Temperature | 85°C                                                                                  |
| Life              | 15000 Hrs (Rated Voltage And Ripple Current At 85C), 24000 Hrs (Rated Voltage At 85C) |
| ESR               | 299 mOhms (100Hz 20C), 167 mOhms (10kHz 20C)                                          |
| Ripple Current    | 2.54 Amps (100Hz 85C), 6.07 Amps (10kHz 85C)                                          |
| Leakage Current   | 1269 uA (5min 20°C)                                                                   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.