



PAGE 1/2	ISSUE 21-09-16A	SERIES SPLITTER	PART NUMBER R434718002
			

All dimensions are in mm.

Weight **152,0000** g
Specification



PAGE 2/2	ISSUE 21-09-16A	SERIES SPLITTER	PART NUMBER R434718002
----------	-----------------	---------------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency range :	6 - 18 GHz
Number of ways	8
Phase	0°
VSWR	
Input	1.6
Output	1.6
Impedance	50 Ohms
Insertion loss	1.5 dB max
Isolation	16 dB mini
Amplitude balance	± 0.5 dB
Phase Balance	± 6°
Average Power	
VSWR load < 1.2	30W
VSWR load : inf	1W

MECHANICAL CHARACTERISTICS

Connectors :	
Input	SMA female
Output	SMA female
Body	Aluminium
Finish	Blue Paint

ENVIRONMENTAL CHARACTERISTICS

Operating temperature	-40 / +85 °C
Storage temperature	-55 / +125 °C