Rigid Industrial BNC Adapter (M/F) - IP68, Black

MODEL NUMBER: **A200-FF-BNC**



Panel-mount adapter changes a male BNC connector to female, allowing a secure link between two male BNC connectors.

Highlights

- IP68 adapter endures immersion in water during harsh weather/industrial conditions
- Nickel connectors with gold contacts resist corrosion that can weaken the signal
- Polarized interface ensures proper mating of locking BNC connectors

Package Includes

A200-FF-BNC Rigid Industrial BNC Adapter (M/F), Black

Features

Connects Coaxial Cabling on Plant Floors and Harsh Outdoor Environments
This rigid industrial adapter (M/F) fastens tightly to a male BNC connector and changes it to female. The A200-FF-BNC is designed for coaxial cables' indoor or outdoor use wherever heavy vibrations, water and dust are present, including industrial plants, warehouses and other manufacturing settings.

IP68 Rating Denotes Resistance to Dust and Water
The IP68 rating means the A200-FF-BNC is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance, keeping the cable safe in storms and other foul weather. The BNC connector locks into place to ensure your AV connection remains stable and secure.

High-Quality Components
The A200-FF-BNC is recommended for transmitting high-definition television signals from cable/satellite boxes. Molded nickel-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission. An included dust cap keeps the adapter free of debris when not in use.

Specifications

OVERVIEW	
UPC Code	037332287083
Technology	Coax
VIDEO	
HDR Support	No
3D Video Supported	No
DisplayPort Alt Mode	No

CONNECTIONS	
Side A - Connector 1	BNC (FEMALE)
Side B - Connector 1	BNC (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Material of Construction	MAIN BODY&DUST CAP: PBT+GF,UL94V-0; ALL HOOD: PVC; CHAIN: BRONZE, NICKEL PLATED
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.04
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154.4°F (-40° to 68°C)
Relative Humidity	10% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
EDID Compatible	No
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
IP68 Rated	Yes
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
Driver Required	No
DIN Mountable	No

Outdoor Use	Yes
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.