

4-Port DisplayPort KVM Switch with Audio, Cables and USB 3.0 SuperSpeed Hub

MODEL NUMBER: **B004-DPUA4-K**



Control 4 DisplayPort computers using one DisplayPort monitor, USB keyboard and USB mouse. Connect USB 3.0 peripherals, such as hard drives and webcams, and share them between computers.

Features

Access and Control Up to 4 Computers with One KVM Switch

- Switch among computers using keyboard hotkeys or front-panel buttons
- Monitor's EDID information sent to connected computer when selected
- Auto Scan feature cycles among computers at regular intervals for at-a-glance observation of activity
- Supports DisplayPort 1.1

Independent Audio Switching

- 3.5 mm mini-stereo speaker and microphone jacks allow sharing of audio equipment among computers
- Listen to audio files on one computer while accessing another computer
- Supports 2-channel stereo audio

Independent USB 3.0 Peripheral Sharing

- 2-port USB 3.0 SuperSpeed hub allows connection of peripherals, such as webcams, flash drives, printers and scanners
- Print documents from one computer while accessing another computer
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1 devices

Compatible with All Major Operating Systems

- Easy to set up with no software or drivers to install
- Supports digital video resolutions up to 2560 x 1600, including 1080p
- Works with Windows, Mac, Linux and Sun
- All necessary cables included

Highlights

- Connect peripherals to built-in 2-port USB 3.0 hub
- Switch among computers via front buttons or keyboard hotkeys
- Supports digital video resolutions up to 2560 x 1600
- Supports DisplayPort 1.1
- Includes all necessary DisplayPort, USB 3.0 and audio cables

System Requirements

- DisplayPort-enabled monitor
- USB keyboard and mouse
- Speaker and microphone with 3.5 mm mini-stereo plugs (for audio)
- Computer with USB port (need USB 3.0 port for USB 3.0 speed)
- Computer with 3.5 mm mini-stereo jacks (for audio)
- Compatible with all major operating systems

Package Includes

- B004-DPUA4-K 4-Port DisplayPort KVM Switch
- (4) DisplayPort cables, 6-ft. (1.83 m)
- (4) USB 3.0 Type-A to Type-B cables, 6-ft. (1.83 m)
- (4) 3.5 mm mini-stereo cables, 6-ft. (1.83 m)
- External power supply (Input: 100/240V, 50/60 Hz, 0.8A; Output: 9V, 2A)
- Universal plug adapters (NEMA 1-15P, CEE 7/16, BS1363, and AS3112)
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332188632
Technology	DisplayPort; Stereo Audio
VIDEO	
Max Supported Video Resolution	2560 x 1600 @60Hz
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
AC Power Adapter Output Specs (V / A)	9V / 2A
AC Power Adapter Cord Length (ft.)	6
AC Power Adapter Cord Length (m)	1.83
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A Output: 9V, 2A
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	6.5
CONNECTIONS	
Number of Ports	4
PC/Server Connections	USB; DisplayPort
Side A - Connector 1	(4) DISPLAYPORT (FEMALE)
Side A - Connector 2	(4) USB 3.0 B (FEMALE)
Side A - Connector 3	(8) 3.5MM (FEMALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
Side B - Connector 2	(2) USB 3.0 A (FEMALE)
Side B - Connector 3	(2) USB A (FEMALE)
Side B - Connector 4	(2) 3.5MM (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	Displayport
Console Keyboard and Mouse Interface	USB



Powering Business Worldwide

TRIPP LITE
SERIES

Console Monitor Interface	Displayport
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (USB); White (Selected PC)
PHYSICAL	
Color	Black
Material of Construction	Steel
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	7.40 x 6.20 x 10.60
Shipping Dimensions (hwd / cm)	18.80 x 15.75 x 26.92
Shipping Weight (lbs.)	5.90
Shipping Weight (kg)	2.68
Unit Dimensions (hwd / in.)	1.800 x 8.100 x 3.900
Unit Packaging Type	Box
Unit Weight (lbs.)	2.1
Unit Weight (kg)	0.95
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0-90% non-condensing
BTUs	22.2 BTU/Hr
COMMUNICATIONS	
IP Remote Access	No
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	Y
Port Selection	Pushbutton; Hotkey
Displayport Specification	1.1
Driver Required	No



Powering Business Worldwide

TRIPP LITE
SERIES

Autoscan Duration	10 TO 60 (DEFAULTS AT 10, USER DEFINABLE IN 10 SECOND INTERVALS)
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; GS; BS; RCM; CB
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.