

## 2-Port DisplayPort to VGA Hub, DP1.2, TAA

MODEL NUMBER: **B157-002-VGA**



Converts and splits a DisplayPort video signal for display on two VGA monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms.

### Description

The B157-002-VGA 2-Port DisplayPort to VGA Splitter converts and splits a DisplayPort video signal for display on two VGA-enabled monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms, this compact splitter features a built-in DisplayPort cable that connects to the source. It lets you use your existing VGA displays instead of buying new DisplayPort monitors or docking stations.

The B157-002-VGA supports video resolutions up to 1080p @ 60 Hz (1920 x 1080), as well as HDCP, EDID and DDC. Orange LEDs next to each output port indicate whether the splitter is powered on and transmitting a signal to the connected displays. The splitter works with all operating systems and is small enough to carry in your backpack or computer bag. Plug-and-play convenience means no software or drivers are needed. An included USB Micro-B cable connects between the source and the splitter to provide power, so no external power supply is required.

### Features

**Converts and Splits DisplayPort Signal to 2 VGA Displays Simultaneously** Ideal for offices, conference rooms, trade shows and classrooms  
**Built-in DisplayPort cable connects to source**  
**Included USB Micro-B cable supplies power to splitter**  
**Save money on new DisplayPort displays or docking stations**

**Top-Shelf Performance** Supports video resolutions up to 1080p @ 60 Hz (1920 x 1080) Complies with HDCP, EDID and DDC  
**LEDs indicate whether splitter is powered on and transmitting signal to connected displays**

**Easy to Use Almost Anywhere** Works with all operating systems  
**Plug and play—no software, drivers or external power supply required**  
**Compact unit fits easily in backpack or computer bag**

### Highlights

- Supports video resolutions up to 1080p @ 60 Hz (1920 x 1080)
- Included USB Micro-B cable supplies power to unit
- Works with all operating systems
- Compact enough for easy carrying in backpack or laptop bag
- Plug and play—no software or drivers required

### Package Includes

- B157-002-VGA 2-Port DisplayPort to VGA Splitter
- USB Micro-B cable, 3 ft.
- Owner's manual

## Specifications

| OVERVIEW     |                       |
|--------------|-----------------------|
| UPC Code     | 037332191496          |
| Product Type | Splitter              |
| Technology   | VGA/SVGA; DisplayPort |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                                  |
|----------------------------------------------|----------------------------------|
| Host Connector                               | DISPLAYPORT (FEMALE)             |
| <b>VIDEO</b>                                 |                                  |
| Max Supported Video Resolution               | 1920 x 1080 (1080p) @ 60Hz       |
| Max Supported Color Depth                    | 24-bit True Color                |
| 3D Video Supported                           | Yes                              |
| <b>AUDIO</b>                                 |                                  |
| Audio Specification                          | 2.0-channel surround sound audio |
| <b>CONNECTIONS</b>                           |                                  |
| Number of Ports                              | 2                                |
| Side A - Connector 1                         | DISPLAYPORT (MALE)               |
| Side A - Connector 2                         | MICRO-USB B (FEMALE)             |
| Side B - Connector 1                         | (2) HD15 (FEMALE)                |
| Connector Plating                            | Nickel                           |
| Input x Output                               | 1 x 2                            |
| Daisy-chainable / Cascadable                 | No                               |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                                  |
| LED Indicators                               | (x2) Orange (Monitor Signal)     |
| <b>PHYSICAL</b>                              |                                  |
| Color                                        | Black                            |
| Material of Construction                     | Metal                            |
| Wire Gauge (AWG)                             | 28                               |
| Cable Length (ft.)                           | 0                                |
| Cable Length (m)                             | 0.00                             |
| Shipping Dimensions (hwd / in.)              | 1.70 x 7.90 x 5.60               |
| Shipping Dimensions (hwd / cm)               | 4.32 x 20.07 x 14.22             |
| Shipping Weight (lbs.)                       | 0.60                             |
| Shipping Weight (kg)                         | 0.27                             |
| Unit Dimensions (hwd / in.)                  | 0.000 x 0.000 x 0.000            |
| Unit Dimensions (hwd / cm)                   | 2.55 x 6.15 x 7.6                |
| Unit Dimensions (hwd / mm)                   | 25.5 x 61.5 x 76                 |
| Unit Weight (lbs.)                           | 0.154                            |
| Unit Weight (kg)                             | 0.07                             |



Powering Business Worldwide

TRIPP LITE  
SERIES

| COMMUNICATIONS                      |                                                                 |
|-------------------------------------|-----------------------------------------------------------------|
| EDID Compatible                     | Yes                                                             |
| FEATURES & SPECIFICATIONS           |                                                                 |
| MST Support                         | No                                                              |
| Displayport Specification           | 1.2                                                             |
| HDCP Specification                  | 1.3                                                             |
| STANDARDS & COMPLIANCE              |                                                                 |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                                                                 |
| Product Warranty Period (Worldwide) | 3-year limited warranty                                         |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.