

Extension Cable for Select Battery Packs, Blue 175A DC Connectors, 1 ft. (0.3 m)

MODEL NUMBER: **BPEXT481**



Adds 1 ft. (0.3 m) to connection between compatible Tripp Lite 48V UPS systems and external battery packs. Required to connect SMART5000XFMRXL and BP48V24-2U in a front-mount configuration in a 4-post 19 in. rack.

Description

The BPEXT481 Extension Cable allows you to connect your SMART5000XFMRXL UPS system and BP48V24-2U battery pack in a front-mount four-post rack configuration in order to extend runtime. It also adds one foot (0.3 meters) to the connection between other compatible 48V UPS systems and external battery packs. The BPEXT481 is constructed using 6 AWG two-conductor black cabling. It features two Blue 175A DC connectors: one output for the battery pack and one input for the UPS system.

Features

Connects SMART5000XFMRXL UPS and BP48V24-2U Battery Pack in Front-Mount Rack

Application

- Compatible with other 48V UPS systems and battery packs
- Heavy-duty 6 AWG 2-conductor black cabling
- 2 Blue 175A DC connectors (1 output, 1 input)
- 1-ft. (0.3 m) in length

Specifications

OVERVIEW	
UPC Code	037332197870
Accessory Type	Extender
Accessory Class	UPS Accessories
INPUT	
Input Connection Type	175A Blue 48V DC Connector (1)

Highlights

- Heavy-duty 6 AWG 2-conductor black cabling
- 2 Blue 175A DC connectors (1 output, 1 input)
- 1-ft. (0.31 m) in length

Package Includes

- BPEXT481 Extension Cable, 1-ft. (0.31 m)



Powering Business Worldwide

TRIPP LITE
SERIES

OUTPUT	
Output Connector Type	175A Blue 48V DC Connector (1)
PHYSICAL	
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	1.40 x 2.40 x 19.40
Shipping Dimensions (hwd / cm)	3.56 x 6.10 x 49.28
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
Unit Weight (lbs.)	1.1
Unit Weight (kg)	0.50
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.