

Full Motion Ceiling Mount for 23" to 42" TVs and Monitors.

MODEL NUMBER: DCTM



Suspends a flat-panel television, monitor or other display from the ceiling, which saves valuable wall and floor space. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants.

Description

The DCTM Full Motion Ceiling Mount saves valuable wall and floor space by suspending your flat-panel television, monitor or other display from the ceiling. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 23 to 42 inches. The DCTM adjusts with one easy touch to customize your viewing at any time. A 90° swivel and -20° tilt capability minimizes glare and provides comfortable viewing from multiple angles. The durable all-metal pole extends from 24 to 34 inches and supports up to 66 lbs (30 kgs). The scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Installation hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 75 mm, 100 x 100 mm, 100 x 200 mm, 200 x 75mm, 200 x 100 mm and 200 x 200 mm.

Features

Save Valuable Wall and Floor Space Suspends flat-panel TV, monitor or other display from ceiling Fits most flat-panel devices from 23 to 42 in. Installation hardware included Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants

Convenient One-Touch Adjustment 90° swivel and -20° tilt capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 66 lbs (30 kgs) Pole extends from 24 to 34 in. Scratch-resistant powder-coated finish blends with any décor

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 75 mm, 100 x 100 mm, 100 x 200 mm, 200 x 75mm, 200 x 100 mm and 200 x 200 mm

Highlights

- Fits most flat-panel displays from 23 to 42 in.
- One-touch adjustment for comfortable viewing
- 90° swivel and -20° tilt for wide range of motion
- Supports up to 66 lbs (30 kgs)

Package Includes

- DCTM
- Hardware packet
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	03733223456



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 100x75; 200x100; 200x200; 200x75; 75x100; 75x200; 75x75
Motion	Full
Mounting Location	Ceiling
Degrees of Motion	-20 Tilt; 90 Swivel
Minimum Screen Size (in.)	23
Minimum Screen Size (cm)	58.42
Maximum Screen Size (in.)	42
Maximum Screen Size (cm)	106.68
Maximum Weight Capacity (lbs.)	66
Maximum Weight Capacity (kg)	30
Min/Max Arm Extension (in.)	24 min to 34 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	21.10 x 9.80 x 20.10
Shipping Dimensions (hwd / cm)	53.59 x 24.89 x 51.05
Shipping Weight (lbs.)	5.30
Shipping Weight (kg)	2.40
Unit Dimensions (hwd / in.)	5.400 x 6.300 x 38.000
Unit Dimensions (hwd / cm)	13.72 x 16 x 96.52
Unit Weight (lbs.)	4.9
Unit Weight (kg)	2.22
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; CE (Europe); REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.