

## Full Motion Flex Arm Desk Clamp for 13" to 27" Monitors

MODEL NUMBER: DDR1327SFC



Mounts a monitor off the surface of your desk, table or workstation to free up valuable space. Ideal for home or office use.

### Description

The VESA-compliant DDR1327SFC Full Motion Flex Arm Desk Clamp attaches to your desk, table or workstation, allowing you to mount a monitor above it and free up valuable workspace. Ideal for home and office, the DDR1327SFC fits most flat-panel displays from 13 to 27 inches.

Swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your monitor to fit your environment and comfort level. Move the screen closer to you, or push it out of your way when not in use. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Durable clamp attaches to most flat surfaces up to 3.5 inches thick with a firm grip. Swivel arm supports up to 22 lbs (9.9 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

### Features

**Attaches to Most Desks, Tables and Workstations**Clamps securely to most flat surfaces up to 3.5 in. thickFits most flat-panel displays from 13 to 27 in. Swivel arm adjusts independently for angle and heightIdeal for home and office use

**Convenient One-Touch Adjustment**180° swivel and -15° to +15° tilt capability provides comfortable viewingFull 360° rotation for viewing in portrait or landscape orientation

**Durable Metal Construction**Supports up to 22 lbs (9.9 kgs)Scratch-resistant powder-coated finish blends with any décorMounting hardware includedDisplay cable attaches to swivel arm with included clips to reduce clutter

**VESA Compliance**Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 22 lbs (9.9 kgs)

### Package Includes

- Adapter bracket assembly
- Pole
- Desk clamp assembly
- (4) M4 screws
- (4) M5 screws
- (4) D5 washers
- Base plate
- Pad
- Hex key, 3 mm
- Hex key, 4 mm
- Owner's manual

## Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332187109
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	10
Number of Displays	1
Shipping Dimensions (hwd / in.)	4.90 x 9.60 x 15.60
Shipping Dimensions (hwd / cm)	12.45 x 24.38 x 39.62
Shipping Weight (lbs.)	8.00
Shipping Weight (kg)	3.63
Unit Dimensions (hwd / in.)	14.370 x 6.290 x 16.930
Unit Dimensions (hwd / cm)	36.50 x 15.98 x 43.00
Unit Weight (lbs.)	5.94
Unit Weight (kg)	2.69
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

5-year limited warranty

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.