

Portable Digital Signage Stand for 32" to 55" Flat-Screen Displays, Folding Portrait/Landscape Mount, Rolling Casters

MODEL NUMBER: **DMPDS3255CF**



Mobile steel TV stand delivers your digital signage message in either portrait or landscape mode.

Features

Take Your Digital Signage Wherever Your Audience Is

This portable TV stand fits most flat-panel displays, whiteboards and monitors from 32 to 55 inches (81 to 140 centimeters). It assembles easily to allow convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels. Reliable rear casters roll smoothly through doorways and over thresholds, allowing you to share your tailored message almost anywhere. The DMPDS3255CF supports both portrait and landscape orientations.

Durable Steel Frame Designed to Last

The frame withstands the stress of repeated adjustments and supports up to 110 pounds (50 kilograms). Because the frame folds when not in use, the DMPDS3255CF is easy to transport and store.

Built-In Cable Management Helps Eliminate Clutter

Equipment cables route through clips on the stand's legs to keep them organized and out of the way. Rubber pads are included to ensure your display remains level on an uneven surface.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75, 100 x 100, 200 x 100, 200 x 200, 300 x 200, 300 x 300 and 400 x 400. All hardware is included.

Specifications

OVERVIEW	
UPC Code	037332263865
Device Compatibility	Monitor/HDTV
PHYSICAL	

Highlights

- Supports most flat-panel monitors and interactive displays from 32 to 55 in.
- Durable steel frame blends into any room decor and supports up to 110 lb.
- Reliable rear casters enable smooth rolling from one location to another
- Foldable stand supports both portrait and landscape viewing
- Cable management clips keep cords organized and prevent cable clutter

Applications

- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session
- Move a flat-panel display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical
- Fold the stand and store it in a secure area when not in use

System Requirements

Flat-screen television, monitor, digital whiteboard or interactive display from 32 to 55 in.

Package Includes

- DMPDS3255CF Portable Digital Signage Stand
- Assembly hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200; 300x200; 300x300; 400x400
Motion	Tilt
Mounting Location	Floor
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.82
Maximum Screen Size (in.)	55
Maximum Screen Size (cm)	139.7
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Number of Displays	1
Unit Dimensions (hwd / in.)	14.700 x 19.900 x 50.900
Unit Dimensions (hwd / cm)	37.3 x 50.5 x 129.3
Unit Weight (lbs.)	77
Unit Weight (kg)	34.93
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.