

FireWire 800 IEEE 1394b Hi-speed Cable (9pin/9pin M/M) 10 ft. (3.05 m)

MODEL NUMBER: **F015-010**



Highlights

- Twice the Speed of Original FireWire - Data Transfers to 800Mbps
- Meets FireWire 800 and 1394b Specifications
- Backward compatible to Original FireWire components

Package Includes

- 10-ft. (3.05 m) IEEE-1394b FireWire 800 Gold Hi-Speed 9pin/9pin Cable

Features

- Data transfer rates to 800Mbps
- Hot Pluggable - supports Plug-n-Play operation
- Premium triple-shielded cable with molded, Gold connectors
- Backward compatible with original FireWire systems and devices
- Compatible with PC, Mac, SUN, and other IEEE-1394b equipped systems

Specifications

OVERVIEW	
UPC Code	037332124616
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	9 PIN (MALE)
Side B - Connector 1	9 PIN (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	0.50 x 5.10 x 8.60



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	1.27 x 12.95 x 21.84
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-14° to 131°F (-25° to 55°C)
Relative Humidity	5 to 90 %
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.