

## Isobar 10-Outlet Home/Business Theater Surge Protector, 8 ft. Cord with Right-Angle Plug, 3840 Joules, LEDs, Metal Housing

MODEL NUMBER: HT10DBS



Premium protection for A/V home or business theater components, including HDTVs and stereo receivers, against dangerous power surges, spikes and line noise. Recommended for medium-to-large home and business theater installations.

### Features

**Network-Grade 3840-Joule Surge Protection for Your Home or Business Theater** Protects your A/V components against even the strongest surges and spikes Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression Exceeds IEEE 587 Category A and B surge suppression specifications

**10 Outlets Accept Wide Range of Electronic Devices** 10 NEMA 5-15R AC outlets accept most home theater equipment 4 widely spaced outlets accommodate bulky transformers without blocking other outlets Included safety covers block accidental contact with unused outlets Color-coded labels make it easy to coordinate outlets with equipment cords

**Isolated Filter Banks Provide Extra Protection** Outlets arranged in 2 exclusive isolated filter banks to limit noise interaction among connected equipment Block disruptive EMI/RFI line noise up to 60 dB that can cause equipment damage or data loss Combine large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

**Protects Coaxial/Telephone/Modem/Ethernet Connections From Surges** 3-line 2.2 GHz gold coaxial protection 1-line telephone/modem protection 1-line high-speed 10/100 Mbps Ethernet protection

**Premium Safety Features** Lighted on/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Diagnostic LEDs confirm power, protection and line fault status at a glance Conforms to current UL 1449 3rd Edition safety standards

**Fits Effortlessly Into Your Setup** 8 ft. (2.4 m) AC power cord reaches nearby outlets Space-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Metal housing designed for long life

**Backed by Ultimate Lifetime Insurance** \$500,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

## Specifications

### Highlights

- 10 NEMA 5-15R outlets in exclusive isolated filter banks
- Network-grade 3840-joule surge protection rating
- Coaxial/telephone/modem/Ethernet surge protection
- 12A resettable circuit breaker prevents dangerous overloads
- 8 ft. power cord with space-saving right-angle NEMA 5-15P plug

### Package Includes

- HT10DBS Isobar 10-Outlet Home/Business Theater Surge Protector, Metal Housing
- RJ11 telephone cable, 6 ft.
- RG59 coaxial cable, 6 ft.
- RJ45 Cat5 Ethernet cable, 6 ft.
- (4) Outlet safety covers
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

| OVERVIEW                           |                                                                               |
|------------------------------------|-------------------------------------------------------------------------------|
| UPC Code                           | 037332121745                                                                  |
| INPUT                              |                                                                               |
| Nominal Input Voltage(s) Supported | 120V AC                                                                       |
| Recommended Electrical Service     | 120V (110-125V)                                                               |
| Input Cord Gauge Type              | 14 gauge; SJT                                                                 |
| Input Cord Gauge (AWG)             | 14                                                                            |
| Voltage Compatibility (VAC)        | 120                                                                           |
| Maximum Surge Amps                 | 150000                                                                        |
| Input Plug Type                    | NEMA 5-15P                                                                    |
| Input Cord Details                 | SJT                                                                           |
| Input Cord Length (ft.)            | 8                                                                             |
| Right-Angle Plug                   | Yes                                                                           |
| Input Cord Length (m)              | 2.44                                                                          |
| Integrated Cord Clip               | No                                                                            |
| OUTPUT                             |                                                                               |
| Frequency Compatibility            | 50 / 60 Hz                                                                    |
| Output (Watts)                     | 1440                                                                          |
| Output Receptacles                 | (10) 5-15R                                                                    |
| Circuit Breaker (amps)             | 12                                                                            |
| Transformer Accommodation          | (6) Yes                                                                       |
| Right-Angle Outlets                | No                                                                            |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                               |
| Diagnostic LED(s)                  | Yes                                                                           |
| Switches                           | Combination AC circuit breaker and illuminated 2 position on/off power switch |
| Diagnostic LED Details             | Built-in LEDs confirm line power, protection and ground status                |
| SURGE / NOISE SUPPRESSION          |                                                                               |
| AC Suppression Joule Rating        | 3840                                                                          |
| AC Suppression Response Time       | NM = instantaneous CM = < 1 ns                                                |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression  |
| UL1449 Let Through Rating          | 330V - UL verified                                                            |
| EMI / RFI Filtering                | Up to 60 dB                                                                   |
| Isolated Filter Banks              | Yes                                                                           |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                                   |                                                                                                                                                             |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Automatic Shut-Off                                | Yes                                                                                                                                                         |
| <b>DATALINE SURGE SUPPRESSION</b>                 |                                                                                                                                                             |
| Telephone/DSL Protection Details                  | 1 line                                                                                                                                                      |
| Cable (Coax) Protection                           | Yes                                                                                                                                                         |
| Cable (Coax) Protection Details                   | 3 line                                                                                                                                                      |
| Network (Ethernet) Protection                     | Yes                                                                                                                                                         |
| Telephone/DSL Protection                          | Yes                                                                                                                                                         |
| <b>PHYSICAL</b>                                   |                                                                                                                                                             |
| Material of Construction                          | Metal                                                                                                                                                       |
| Power Cord Color                                  | Black                                                                                                                                                       |
| Housing Color                                     | Black                                                                                                                                                       |
| Mounting Holes or Slots                           | Yes                                                                                                                                                         |
| Slot or Hole Mount Measurement (Center to Center) | Distance between horizontal tabs = 355.09 mm; Distance between vertical tabs = 58.17 mm                                                                     |
| Outlets Measurement (Center to Center)            | Distance between horizontal standard outlets = 39.45mm; Distance between horizontal transformer outlets = 53mm; Distance between vertical outlets = 38.76mm |
| Receptacle Color                                  | Black                                                                                                                                                       |
| Shipping Dimensions (hwd / in.)                   | 16.50 x 3.10 x 9.20                                                                                                                                         |
| Shipping Dimensions (hwd / cm)                    | 41.91 x 7.87 x 23.37                                                                                                                                        |
| Shipping Weight (lbs.)                            | 4.60                                                                                                                                                        |
| Shipping Weight (kg)                              | 2.09                                                                                                                                                        |
| Unit Dimensions (hwd / in.)                       | 2.500 x 14.500 x 3.500                                                                                                                                      |
| Unit Dimensions (hwd / cm)                        | 36.2 x 2 x 5.7                                                                                                                                              |
| Unit Weight (lbs.)                                | 3.5                                                                                                                                                         |
| Unit Weight (kg)                                  | 1.59                                                                                                                                                        |
| <b>COMMUNICATIONS</b>                             |                                                                                                                                                             |
| Network Compatibility                             | 100 Mbps (Fast Ethernet)                                                                                                                                    |
| <b>FEATURES &amp; SPECIFICATIONS</b>              |                                                                                                                                                             |
| Rotatable Outlets                                 | No                                                                                                                                                          |
| Antimicrobial                                     | No                                                                                                                                                          |
| <b>STANDARDS &amp; COMPLIANCE</b>                 |                                                                                                                                                             |
| Product Certifications                            | CAN/CSA-C22.2 No. 269.3 (Canada); UL 1449; UL 497A                                                                                                          |
| Product Compliance                                | FCC Part 68; RoHS                                                                                                                                           |



Powering Business Worldwide

TRIPP LITE  
SERIES

WARRANTY & SUPPORT

|                                                            |                                                                                                                          |
|------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                                                                                                |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$500,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.