

12-Port Wall-Mount Cat5e Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N050-012



Highlights

- Easy wallmounting with included 89B bracket
- 12 Cat5e Rated Jacks
- 110 Punch down on rear of panel
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat5e Wall Mount Patch Panel 568B-12 Port
- Mounting Bracket

Description

This Cat5e wall-mount patch panel guarantees compatibility with all networks. Color-coded for both EIA/TIA 568A and 568B installations. Panel comes with 110-type termination blocks. This 12-inch panel effortlessly mounts to a wall or desk with two "C" brackets. Mounting bracket is provided. UTP Cat5e 22-24 AWG solid cable

Features

- Cat5e
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named.
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Includes mounting bracket

Specifications

OVERVIEW	
UPC Code	037332013170
Product Type	Wall Mount
Technology	Cat5/5e
CONNECTIONS	
Number of Ports	12
Side A - Connector 1	110 IDC



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
PHYSICAL	
Shipping Dimensions (hwd / in.)	11.02 x 3.15 x 2.17
Shipping Dimensions (hwd / cm)	27.99 x 8.00 x 5.51
Shipping Weight (lbs.)	0.68
Shipping Weight (kg)	0.31
Unit Dimensions (hwd / in.)	3.330 x 10.000 x 1.900
Unit Dimensions (hwd / cm)	8.38 x 25.4 x 4.83
Panel Style	Punchdown
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.