

SmartRack 2U Hinged Wall-Mount Patch Panel Bracket

MODEL NUMBER: N060-002



Highlights

- Laser cut 14-gauge steel results in smooth edges
- Keyholes on 16-inch centers plus through-the-wall cabling cut-out
- Accepts any standard 19inch Patch Panels
- 2U Height (3.50"): 19"wide x 3.50" high x 6.0" deep

Package Includes

- 2U Wallmount Patch Panel Bracket
- Pkg 10 mounting screws

Description

This heavy-duty 14-gauge-steel 2U wall-mount patch panel bracket is the ideal alternative to a full size rack. Standard EIA 19-inch width allows installation of any 19-inch patch panel. Laser-cut metal keeps all edges smooth, greatly reducing the possibility of injury and wear on cable jackets. Universal mounting for right or left hinging. Keyholes are spaced 16 inches apart for mounting on wall studs. Stamped horizontal reinforcement ribs allow for greater sturdiness and stability and allow the addition of a rear cutout for feeding cable through a wall opening. Smooth, glossy black finish.

Features

- 2U Height (3.50"), 6inch depth
- Laser cut for smooth edges
- 16 -inch center mounting
- Universal left or right hinge mounting
- Rear cut-out for through the wall cabling
- Standard EIA 19inch width accepts any manufacturers EIA compliant patch panel
- Smooth, black glossy finish
- Heavy duty 14 gauge steel with stamped reinforcement ribs

Specifications

OVERVIEW	
UPC Code	037332126399
Accessory Type	Mounting Bracket
Accessory Class	Rack Accessories
PHYSICAL	
Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Rack Height	2U
Maximum Device Depth (cm)	13.97
Maximum Device Depth (in.)	5.5
Maximum Device Depth (mm)	140
Shipping Dimensions (hwd / in.)	4.10 x 20.30 x 6.70
Shipping Dimensions (hwd / cm)	10.41 x 51.56 x 17.02
Shipping Weight (lbs.)	2.90
Shipping Weight (kg)	1.32
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	8.89 x 48.26 x 15.24
Unit Weight (lbs.)	2.5
Unit Weight (kg)	1.13
Weight Capacity - Stationary (kg)	8
Weight Capacity - Stationary (lbs.)	17
STANDARDS & COMPLIANCE	
Product Certifications	IEC 60297-3; NOM (Mexico); UL 60950-1
Product Compliance	DIN 41494; EIA/ECA-310-E; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.