


12-Port Wall-Mount Patch Panel for UTP Keystone Jacks, Rotatable Modules, TAA

MODEL NUMBER: **N062-012-KJ-WM**



Manages and organizes input/output network cable connections in a variety of applications, including audio/video, VoIP, Ethernet and USB.

Features

Manages and Organizes up to 12 Cable Connections

This 12-port patch panel is ideal for small network closets or wall mounting. Twelve blank cutouts accommodate almost any standard keystone jack, including RJ45 Ethernet, HDMI and USB. Ports are numbered to help you identify each connection at a glance.

Designed for Easy Custom Installation

Flexible horizontal or vertical mounting styles let you install the ABS plastic N062-012-KJ-WM where best needed and organize its inputs to specific requirements. The twelve cutouts are organized into six rotating bezels, which let you swivel each connection to a specific direction.

TAA-Compliant for GSA Schedule Purchases

The N062-012-KJ-WM is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332283405
Product Type	Wall Mount
Technology	Cat5/5e; Cat6; Cat6a; Cat8
Country/Region	Global
CONNECTIONS	
Ports	12
Ports Detail	Swivel portsRotation angle ±27°

Highlights

- 12 blank cutouts accommodate all UTP keystone jacks, including RJ45, HDMI and USB
- Mounts to wall vertically or horizontally with included 89B bracket
- Ports are numbered for at-a-glance connection identification
- High-impact ABS construction designed to blend in with your home/office decor
- Recommended for AV, VoIP, Ethernet and other applications in small network closets

Package Includes

- 12-Port Wall-Mount Patch Panel
- Mounting bracket



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	ABS
Mounting Location	Wall; Ceiling
Mounting Holes or Slots	Yes
Total Number of Ports	12
Unit Dimensions (hwd / in.)	3.338 x 10.000 x 2.823
Unit Dimensions (hwd / cm)	7.17 x 8.48 x 25.42
Unit Dimensions (hwd / mm)	71.7 x 84.8 x 254.2
Unit Packaging Type	Box
Mounting Details	Included 89B mounting bracket allows cables to be routed behind the installation
Cable Entry/Exit	Cables exit from the rear of the product.
Panel Style	Blank
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Relative Humidity	10% to 85% RH
FEATURES & SPECIFICATIONS	
Mounting Accessory Included	No
Antibacterial	No
Breakout	No
Numbered Ports	Yes
Driver Required	No
Recommended Category Cable	Cat5, Cat6, Cat6a, Cat8
Keystone Jacks	Yes
Labeled Ports	No
Panel Applications	Ethernet
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.