

24-Port Cat6/Cat5 Low Profile Feed-Through Patch Panel, 1U Rack-Mount/Wall-Mount, TAA

MODEL NUMBER: N250-024-LP



Easy Cat6 Cable patching with right-angle couplers

Description

The N250-024-LP Cat6 Feed-Through Low-Profile Patch Panel makes cable patching quick and easy by simply plugging Cat6 Ethernet cables into either side of the Cat6 couplers. Ninety-degree angles on the couplers allows for low-profile mounting to a wall with included stand-off brackets. Cables feed into the front of the panel, and corresponding Ethernet cables exit Up, Down, Left or Right, depending on the mounting position. Patented printed circuit board design within the coupler exceeds NEXT requirements for Cat6 component testing, assuring Gigabit+ speeds.

Features

- 24-port Feed-through panel for Cat6 or Cat5e networks
- Wall or Rack mountable (standoff brackets included for wall mounting)
- 19" Wide by 1.75" (1U) High x 1.42" deep
- Ninety degree coupler allows a multitude of mounting angle options
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332171139
Product Type	Rackmount
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	24
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)

Highlights

- 90 degree Cat6 RJ45 jacks allows easy cable routing
- Wall mountable with standoff brackets, or rack mountable
- Exceeds TIA-EIA-568-C.2 Cat6 Component requirement
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

24-port Cat6 Low Profile Feed-Through Patch Panel



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 3.00 x 19.60
Shipping Dimensions (hwd / cm)	6.35 x 7.62 x 49.78
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Panel Style	Feed-Through
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.