

Enclosure for 5 High-Density Fiber Cassettes, 1U

MODEL NUMBER: **N482-01U**

Description

The N482-01U is a high-density Fiber Cassette solution that supports up to five high-density Fiber Cassettes, maximizing rack space and allowing for up to 60 Duplex LC Ports (120 fiber connections) in just 1U of space. High-density Fiber Cassettes come in multiple variations, allowing you to connect different generations of equipment (10 Gb, 40 Gb, 100/120 Gb), and giving you the flexibility to adapt as your technology changes. Installation is simple, with the cassettes being easily installed or removed using push/pull tabs to lock or unlock them from the panel; no tools required. Management is a breeze with an optional rear-mounting cable management bracket that allows you to rout your cabling neatly and safely. A fold-down door panel is featured on the front of the unit, and protects your connections, while rotating out of the way to provide full access. The door panel can also be removed altogether for installations where constant access is preferred. Constructed of heavy-duty steel housing.

Features

- Space saving 1U design, 19-inch rack-mountable
- Supports up to 5 High Density Fiber Cassettes, allowing for up to 60 Duplex LC Ports (120 fiber connections), making the most of your rack space
- Cassettes come in multiple variations, allowing you to connect different generations of equipment (10 Gb, 40 Gb, 100/120Gb), and giving you the flexibility to adapt as your technology changes.
- Includes optional rear-mounting cable management bracket for proper routing of cabling
- Features a fold-down door panel on the front of the unit that protects your connections, while rotating out of the way to provide full access. Door panel can also be removed altogether.
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
UPC Code	037332184511
Technology	Singlemode; Multimode
PHYSICAL	
Color	Black

Highlights

- Space saving 1U design, 19" rack-mountable
- Supports up to 5 High Density Fiber Cassettes, allowing for up to 60 Duplex LC Ports (120 fiber connections), making the most of your rack space
- Includes optional rear-mounting cable management bracket for proper routing of cabling
- Features a fold-down door panel on the front of the unit that protects your connections, while rotating out of the way to provide full access. Door panel can also be removed altogether.

Package Includes

- N482-01U High Density Fiber Enclosure Panel, 1U, 5-Cassette Capacity
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	3.50 x 15.00 x 21.10
Shipping Dimensions (hwd / cm)	8.89 x 38.10 x 53.59
Shipping Weight (lbs.)	6.60
Shipping Weight (kg)	2.99
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 13.000
Unit Dimensions (hwd / cm)	4.445 x 48.26 x 33.02
Unit Weight (lbs.)	4.5
Unit Weight (kg)	2.04
Panel Style	Cassette Type
ENVIRONMENTAL	
Operating Temperature	-4 to 140 F (-20 to 60 C)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.