

# 16-Port Fiber Patch Panel, 1U (SC/SC), Multimode or Singlemode

MODEL NUMBER: **N490-016-SCSC**



## Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125, 50/125, and Singlemode 9/125
- 16 ports in 1U of rackspace

## Package Includes

- 16 Port SC/SC Duplex Multimode / Singlemode Fiber Optic Patch Panel

## Description

This 16-port 1U rack-mount SC/SC Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-thru duplex multimode connectors are mounted on a 16-gauge, cold rolled, black powder coated steel panel. Use with 62.5/125 or 50/125 multimode fiber Ethernet cables, as well as 9/125 Singlemode. Panel measures 19 inches wide by 1.75 inches high.

## Features

- 16 ports SC/SC
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 Multimode fiber patch cables, and 9/125 Singlemode
- Available in ST/ST, SC/SC, LC/LC,

# Specifications

| OVERVIEW             |                    |
|----------------------|--------------------|
| UPC Code             | 037332135322       |
| Product Type         | Feed-Through       |
| Technology           | Multimode          |
| CONNECTIONS          |                    |
| Number of Ports      | 16                 |
| Side A - Connector 1 | SC DUPLEX (FEMALE) |
| Side B - Connector 1 | SC DUPLEX (FEMALE) |
| PHYSICAL             |                    |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / in.)     | 4.00 x 3.00 x 21.70       |
| Shipping Dimensions (hwd / cm)      | 10.16 x 7.62 x 55.12      |
| Shipping Weight (lbs.)              | 1.30                      |
| Shipping Weight (kg)                | 0.59                      |
| Panel Style                         | Pass-Through              |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.