

PDU Power Cord, C13 to P-Lock C14 - North America and Europe Rated, 10A, 250V, 18 AWG, 3 ft. (0.9 m), Black

MODEL NUMBER: P004-E03



Connects a computer, server or switch to a PDU with a P-Lock C13 or C39 power connector and extends your existing power connection by 3 ft.

Features

Locking C13-to-C14 Power Cable Connects Computers and Servers to a PDU

The P004-E03 power extension cord can be used to power a computer, server, switch or other device commonly found in a small data center, office workstation or other lower-amp application. The three-foot (0.9-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure. It complies with UL and VDE standards for international application use.

Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock C14 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C13 and C39 outlets. The P-Lock connection helps reduce costly downtime caused by accidental cable disconnections in a crowded rack or PDU space. The P004-E03 lets you replace a non-locking C14/C13 cable or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

Specifications

OVERVIEW	
UPC Code	037332292933
Product Type	PDU Power Cord
Device Compatibility	Computer; Server; Network Switch; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10

Highlights

- Recommended for powering computers, servers and other network devices
- P-Lock C14 connector eliminates accidental cable disconnections in a crowded PDU
- 3 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter
- PDU-style cord replaces or upgrades non-locking power cable provided by manufacturer
- Complies with UL and VDE standards for use in international applications

Package Includes

P004-E03 PDU Power Cord, C13 to P-Lock C14, 3 ft. (0.9 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	H05VV-F; SJT; VW-1
Power Cord Jacket Type	SJT + H05VV-F
Cable Outer Diameter (OD)	7.0mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.0
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Weight (lbs.)	0.82
Shipping Weight (kg)	0.37
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 158°F (-5° to 70°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Relative Humidity	35 TO 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
P-Lock Power Cord	Yes
Locking Power Cord	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS3; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.