

Y Splitter Power Cable, NEMA 5-15P to 2x C13 - 10A, 125V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P006-006-2



Power cord splitter allows two devices with C14 inlets to share one AC power input cord and one NEMA 5-15R outlet.

Features

Y-Style Power Cord Splitter Connects 2 Devices with C14 Inlets to One AC Outlet This computer power cord splitter allows two devices with C14 power inlets to share one AC input cord and one NEMA 5-15R outlet. The AC power splitter features a NEMA 5-15P plug for connecting to an AC power source and two C13 ends for connecting to devices. By connecting two devices to one outlet, the 6-ft. (1.83 m) power cord splitter frees up space in a PDU or surge protector and allows welcome flexibility in placing equipment with respect to the power outlet.

Dual IEC Cable Powers a Wide Variety of Essential Electronics With this PC power splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual IEC power cable is compatible with power and extension cords.

Specifications

OVERVIEW	
UPC Code	037332148971
Device Compatibility	Computer; Monitor/HDTV; Printer; Scanner; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing Y splitter power cable
- NEMA 5-15P plug connects to AC power; C13 plugs connect to devices' C14 inlets

Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 6-ft. (1.83 m) away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

Package Includes

- P006-006-2 Y Splitter Power Cable, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	(2) IEC-320-C13
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 1.27
Shipping Weight (lbs.)	0.77
Shipping Weight (kg)	0.35
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.