

## Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 10A, 125V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: **P006-006-HG10**



Connects your PC, mobile cart or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

### Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Designed and Tested to Strict Hospital-Grade Standards** This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

## Specifications

OVERVIEW	
UPC Code	037332193254
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG

### Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Medical power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

### Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 6-ft. (1.83 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P006-006-HG10 Hospital-Grade Power Cord, NEMA 5-15P to C13, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C13
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.00 x 9.90 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 25.15 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.