

## Computer Power Cord, NEMA 5-15P to C13 - Heavy-Duty, 15A, 125V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P007-010**



Computer power cord connects a server, computer, monitor, printer or other device with a C14 inlet to an AC outlet on a PDU.

### Features

**5-15P to C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This computer power supply cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. You can use it to connect a computer, server, monitor, laser printer or drive to a PDU, UPS, surge protector or AC wall outlet. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

## Specifications

| OVERVIEW                    |   |
|-----------------------------|---|
| UPC Code                    | 037332140913                                      |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region              | North America                                     |
| INPUT                       |   |
| Maximum Input Amps          | 15  |
| Voltage Compatibility (VAC) | 125   |
| CONNECTIONS                 |   |
| Side A - Connector 1        | NEMA 5-15P  |
| Side B - Connector 1        | IEC-320-C13                                       |

### Highlights

- Recommended for powering larger servers, laser printers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Computer power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, large servers and laser printers to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P007-010 Desktop Computer Power Cord, 5-15P to C13, 10-ft. (3.05 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                            |                             |
|-------------------------------------|-----------------------------|
| Plug Color                          | Black                       |
| Cable Jacket Color                  | Black                       |
| Cable Jacket Material               | PVC                         |
| Cable Jacket Rating                 | VW-1                        |
| Power Cord Jacket Type              | SJT                         |
| Cable Outer Diameter (OD)           | 9.3mm                       |
| Number of Conductors                | 3                           |
| Wire Gauge (AWG)                    | 14                          |
| Wire Gauge (OD - mm <sup>2</sup> )  | 2.08                        |
| Cable Length (ft.)                  | 10                          |
| Cable Length (m)                    | 3.05                        |
| Shipping Dimensions (hwd / in.)     | 1.00 x 7.00 x 11.00         |
| Shipping Dimensions (hwd / cm)      | 2.54 x 17.78 x 27.94        |
| Shipping Weight (lbs.)              | 1.06                        |
| Shipping Weight (kg)                | 0.48                        |
| ENVIRONMENTAL                       |                             |
| Operating Temperature Range         | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range           | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range            | 10% to 65% RH               |
| Storage Humidity Range              | 10% to 65% RH               |
| FEATURES & SPECIFICATIONS           |                             |
| Antibacterial                       | No                          |
| Angled Plug                         | No                          |
| High Voltage                        | No                          |
| Locking Plug                        | No                          |
| Coiled Power Cord                   | No                          |
| STANDARDS & COMPLIANCE              |                             |
| Product Certifications              | cUL Listed; UL Listed       |
| Product Compliance                  | RoHS                        |
| WARRANTY & SUPPORT                  |                             |
| Product Warranty Period (Worldwide) | Lifetime limited warranty   |



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.