

IEC C14 to IEC C7 Power Cord Adapter - 7A, 125V, Black

MODEL NUMBER: P016-000



C14 to C7 adapter connects your notebook or laptop with a 2-slot C8 power connector to a C13 outlet on a surge protector or UPS.

Features

IEC C14 to IEC C7 Adapter Connects Notebook Computers to an AC Outlet This UL-listed C14 to C7 power cord adapter converts a C8 plug into a C14 connector and is ideal for a device's built-in power cord that doesn't match an available outlet. You can use this adapter to connect a notebook computer, laptop or other device with a two-slot C8 power cord to a surge protector or UPS system with a C13 outlet.

Specifications

OVERVIEW	
UPC Code	037332217981
Product Type	Computer Power Adapter
Device Compatibility	Laptop; Computer; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	7
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C7 (NON-POLARIZED)
Connector Style	Straight

Highlights

- Recommended for powering notebook computers and laptops with C8 inlets
- Converts a C8 connector into a C14 connector to match an available outlet

Applications

- Connect a laptop or notebook computer to a C13 outlet near your workstation
- Connect a laptop or notebook to a surge protector at a trade show or lecture hall

Package Includes

- P016-000 IEC C14 to IEC C7 Power Cord Adapter, Black



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	N/A
Power Cord Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	30% to 80% RH
Storage Humidity Range	30% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.