

## Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: **P022-003**



3 ft. extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

### Features

**Three-Foot Extension Cord Connects Computers, Printers, Servers and Other Equipment** This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to three feet for more flexibility in placing a device. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

## Specifications

OVERVIEW	
UPC Code	037332205933
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
PHYSICAL	

### Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Adds 3-ft. (0.91 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 3-ft. (0.91 m) extension cord

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P022-003 Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 3 ft., Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	0.33
Shipping Weight (kg)	0.15
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.