

Power Extension Cord, C20 to C19 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.6 m), Red

MODEL NUMBER: **P036-002-ARD**



C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

Features

20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection

This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot (0.6-meter) length helps reduce cable clutter and minimize the risk of tripping.

Red Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cable has a red PVC jacket, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cable from becoming accidentally disconnected.

Specifications

OVERVIEW	
UPC Code	037332288998
Device Compatibility	Network Switch; PDU; Router; Server; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C20

Highlights

- Recommended for powering servers, routers and other high-output network devices
- Red cable jacket allows quick identification of devices in a crowded rack enclosure
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Package Includes

P036-002-ARD C19 to C20 Heavy-Duty Extension Cord, 2 ft. (0.6 m), Red



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C19
PHYSICAL	
Plug Color	Red
Cable Jacket Color	Red
Connector Color	Red
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.2mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	1.5
Cable Length (ft.)	2
Cable Length (m)	0.61
Cable Length (in.)	24
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.93
Shipping Weight (kg)	0.42
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 65% RH
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Certifications	UL Listed
Product Compliance	WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.