

Power Extension Cord/Splitter, NEMA L6-20P to 2x NEMA L6-20R Y Splitter, Heavy-Duty - 20A, 250V, 10 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: **P039-001-2**



L6-20P to L6-20R splitter allows two devices with NEMA L6-20P plugs to share one AC power input cord and one NEMA L6-20R outlet.

Features

Heavy-Duty Y-Style Splitter Cables Connects 2 Devices with L6-20P Plugs to One AC Outlet This Y splitter cable features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. With this extension cord splitter, a single NEMA L6-20R outlet can power two devices, such as PDUs, UPS systems, instrument amplifiers and other equipment compatible with a NEMA L6-20P plug. Ideal for areas where AC outlets are limited, such as rack cabinets or small network closets, this L6-20P to L6-20R Y splitter is compatible with most power and extension cords. The 1-ft. (0.3 m) length helps reduce cable clutter.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Specifications

OVERVIEW	
UPC Code	037332148025
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	100-250

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual PDUs, UPS systems or other heavy-duty devices
- Adds 1-ft. (0.31 m) to your existing power connection to provide flexibility in placing devices
- Locking connectors maintain secure link to avoid loss of power and costly downtime
- Thick 10 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect 2 devices like PDUs and UPS systems to one power outlet up to 1-ft. (0.31 m) away in your office or work space
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

P039-001-2 L6-20P to 2x L6-20R Y Splitter, 1-ft. (0.31 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	NEMA L6-20P
Side B - Connector 1	(2) NEMA L6-20R
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	14.5mm
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	19.70 x 15.80 x 0.50
Shipping Dimensions (hwd / cm)	50.04 x 40.13 x 1.27
Shipping Weight (lbs.)	2.09
Shipping Weight (kg)	0.95
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 70% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.