

Power Extension Cord, NEMA L5-30P to NEMA L5-30R- Heavy-Duty, 30A, 125V, 10 AWG, 6 ft. (1.83 m), Black, Locking Connectors

MODEL NUMBER: P046-006-LL-30A



Extends the length of your existing power cord with NEMA L5-30P plug by 6 ft.

Description

The P046-006-LL-30A Heavy-Duty Power Extension Cord features a NEMA L5-30P plug on one end and a NEMA L5-30R receptacle on the other, allowing you to extend the length of your existing power cord. Both molded connectors twist and lock into place, which prevents disconnection via jostling or other accidental impact. The 6-ft. (1.83 m) 10 AWG cord is rated for 125V and 30A. Its durable PVC jacket is designed to last a long time.

Features

Extends Existing Power Cord with NEMA L5-30P Plug

- NEMA L5-30R receptacle at opposite end
- Molded locking connectors prevent accidental disconnection
- Integral strain relief
- 125V/30A rating
- Durable PVC jacket
- 6-ft. (1.83 m) long

Highlights

- Locking connectors prevent accidental disconnection
- Durable PVC jacket
- 6-ft. (1.83 m) long
- 125V/30A rating

Package Includes

- P046-006-LL-30A Heavy-Duty Power Extension Cord, 6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332200938
Device Compatibility	UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	30



Powering Business Worldwide

TRIPP LITE
SERIES

Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-30R
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	14.6mm
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (cm)	182.88
Shipping Dimensions (hwd / in.)	11.50 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	29.21 x 22.86 x 1.27
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	Yes
Coiled Power Cord	No
Locking Power Cord	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

P-Lock Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.