

Power Cord Adapter, NEMA L5-20P to NEMA 5-20R - Heavy-Duty, 20A, 125V, 12 AWG, 6-in. (15.24 cm), Black

MODEL NUMBER: P046-06N



Heavy-duty extension cord connects your computer or other device with a NEMA 5-20P plug to a NEMA L5-20R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This six-inch cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA 5-20P plug to a wall outlet, PDU or UPS system with a NEMA L5-20R outlet. The short length helps reduce cable clutter.

Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Specifications

OVERVIEW	
UPC Code	037332158321
Product Type	Computer Power Adapter
Device Compatibility	Computer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	125

Highlights

- Recommended for powering computers, servers and other network devices
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P046-06N L5-20P to 5-20R Heavy-Duty Extension Cord, 6 in., Black



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	NEMA L5-20P
Side B - Connector 1	NEMA 5-20R
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Power Cord Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.