

## DisplayPort to VGA Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **P134-06N-VGA**



### Features

- Connect a VGA monitor to a computer with a Displayport output
- DisplayPort to VGA Active Cable Adapter - 1920x1200/1080P (DisplayPort-Male to HD15-Female) - 6 in.
- Plug and Play - no drivers or setup needed
- Supports PC video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards that do not output Dual Mode (DP++) signals, such as AMD Eyefinity
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

### Highlights

- Connect a VGA monitor to a computer with a Displayport output
- DisplayPort to VGA Active Cable Adapter - 1920x1200/1080P (DisplayPort-Male to HD15-Female) - 6 in.
- Plug and Play - no drivers or setup needed
- Supports PC video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards that do not output Dual Mode (DP++) signals, such as AMD Eyefinity
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

### System Requirements

- Computer with a Displayport output
- Monitor with a VGA port
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-VGA-V2

### Package Includes

- DisplayPort to VGA Active Cable Adapter - 1920x1200/1080P (DisplayPort-Male to HD15-Female) - 6 in.

## Specifications

OVERVIEW	
UPC Code	037332159151
Product Type	Video Adapter
Technology	VGA/SVGA; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.