


## Keyspan Mini DisplayPort to DisplayPort Adapter Cable (M/F), 4K 60 Hz, DP 1.2, HDCP 2.2, 10 ft. (3.1 m)

MODEL NUMBER: P139-010-DP-V2B



Connects a computer with a Mini DisplayPort (mDP) output to a high-definition monitor, projector or television with a DisplayPort™ input.

### Description

The P139-010-DP-V2B Keypspan® Mini DisplayPort 1.2a to DisplayPort Cable Adapter and Video Converter connects an mDP computer to a high-definition DisplayPort monitor, projector or television. It allows you to continue using your existing DisplayPort display instead of buying a new Mini DisplayPort monitor.

Ideal for displaying crystal-clear video on a large monitor or digital sign, this 10-ft. (3.05 m) cable supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, including 1080p. Nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and molded connectors last a long time. Just plug and play with no software or drivers required.

### Features

#### Sends UHD Mini DisplayPort Audio/Video to a DisplayPort Monitor

- Connects an mDP computer to a DisplayPort monitor, projector or TV
- Recommended for displaying Mini DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing DisplayPort display, instead of buying a new monitor

#### Vibrant Video Quality

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz, including 1080p
- Compliant with HDCP 2.2 and DisplayPort 1.2a

#### Superior Materials for Superior Performance

- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Integral strain relief for long life
- Plug and play—no software or drivers required

## Specifications

### Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Nickel-plated connectors with gold-plated contacts
- Integral strain relief
- Compliant with HDCP 2.2 and DisplayPort 1.2a
- Plug and play—no software or drivers required

### Package Includes

- P139-010-DP-V2B Keypspan Mini DisplayPort 1.2a to DisplayPort Cable Adapter (M/F), 10-ft. (3.05 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332201782
Product Type	Passive Cable
Technology	DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
PHYSICAL	
Color	White
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Cable Length (cm)	304.80
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-85% non-condensing
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.