

3.5 mm 3-Position to 3.5 mm 4-Position Audio Headset Splitter Adapter Cable (2xF/M), 6 in. (15.2 cm)

MODEL NUMBER: **P318-06N-MFF**



Connect a set of speakers and microphone to the 4-position combo audio jack on your computer, laptop or mobile device

Features

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief
- Constructed of 28AWG wire
- Features a compact design perfect for tucking into your laptop bag when you're on the go

Specifications

OVERVIEW	
UPC Code	037332184047
Product Type	Passive Cable
Technology	Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE)
Side B - Connector 1	(2) 3.5MM (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	

Highlights

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief

Package Includes

- 6-in. 4-Position Male to (x2) 3-Position Female Audio Adapter Cable



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.