

## VGA Monitor Extension Cable, 640x480 (HD15 M/F), 25 ft. (7.62 m)

MODEL NUMBER: **P510-025**



### Description

VGA monitor extension cable will extend the reach of a monitor cable by an additional 25 feet (7.6 meters). Gold-plated connectors and gold-plated copper contacts ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time.

For use with monitors with resolutions up to 640 x 480 ( VGA Std ). For higher resolution monitors, please use P500-025.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

## Specifications

OVERVIEW	
UPC Code	037332123015
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No

### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

### System Requirements

<ul><li style="line-height: 12px; margin-bottom: 7px;">Monitor with HD15 cable and resolutions up to 640x480

### Package Includes

- 25-ft. (7.62 m) VGA Monitor Extension Gold Cable HD15F to HD15M



*Powering Business Worldwide*

TRIPP LITE  
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (in.)	300
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.