

# HDMI to VGA Active Adapter Cable (HDMI to Low-Profile HD15 M/M), 3 ft. (0.9 m), TAA

MODEL NUMBER: P566-003-VGA



Converts an HDMI video signal for presentation on an existing VGA monitor, projector or television, saving you the time, effort and expense of upgrading to a new HDMI display.

## Features

### Send High-Definition HDMI Video Signals to a VGA Display

- Connects HDMI source to a VGA monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile HD15 connector fits neatly into tight spaces
- Plug-and-play—no software or drivers necessary

### Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz

### Superior Materials for Superior Performance

- Foil and braid shielding for reliable protection from EMI/RFI line noise
- Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Impedance-matched twisted-pair construction reduces crosstalk and interference
- USB Micro-B port provided in case additional power is needed

In certain applications, it is necessary to provide additional power to the adapter by using a Micro-USB cable to a USB wall charger. It is also suggested to manually set the same Refresh Rate and Resolution settings on your Source and VGA devices.

## Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Gold-plated HDMI connector for maximum conductivity
- Foil and braid shielding for reliable EMI/RFI line noise protection
- Low-profile VGA connector fits neatly into tight spaces
- Plug-and-play with no software or drivers required

## System Requirements

- Computer or other source with HDMI female connector
- Monitor or other display with VGA female connector
- USB Micro-B to A cable and USB power source (only if additional power is needed)

## Package Includes

- P566-003-VGA HDMI to VGA Active Converter Cable, 3 ft.

## Specifications

OVERVIEW	
UPC Code	037332201126
Product Type	Active Cable
Technology	HDMI; VGA/SVGA



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Type	Active
<b>VIDEO</b>	
Max Supported Video Resolution	1920 x 1200 (1080p)
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (MALE) - LOW PROFILE; MICRO-USB B (FEMALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.