

Standard Speed HDMI Cable with Ethernet, Digital Video with Audio (M/M), 50 ft. (15.24 m)

MODEL NUMBER: P569-050



Highlights

- 50-ft. (15.24 m) Standard Speed with Ethernet HDMI cable
- Supports transmission speeds up to 10.2Gbps
- Backward compatible to previous HDMI generations
- Video mirroring with iPad2

System Requirements

- HDMI video source and HDMI enabled TV / Monitor

Package Includes

50-ft. (15.24 m) Standard Speed with Ethernet HDMI Cable

Features

- 50-ft. (15.24 m) Standard Speed with Ethernet HDMI cable
- Supports transmission speeds up to 10.2Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

Specifications

OVERVIEW	
UPC Code	037332186041
Product Type	Passive Cable
Technology	HDMI
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz
Max Supported Color Depth	48-bit Deep Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Signal Transmission	Bidirectional
AUDIO	
Audio Specification	ARC
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	0
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	7.3 mm
Wire Gauge (AWG)	28
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Ferrite Core	No
Minimum Bend Radius	36.5mm
Shipping Dimensions (hwd / in.)	2.20 x 6.80 x 8.00
Shipping Dimensions (hwd / cm)	5.59 x 17.27 x 20.32
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	2.200 x 6.800 x 8.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)



Powering Business Worldwide

TRIPP LITE
SERIES

Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Armored Cable	No
Ethernet Support	Yes
HDCP Specification	1.4; 2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.