

Signal Booster Strength

In some applications, a signal booster (Model Number: B121-000) should be used with this cable to ensure a signal strong enough for your display.

DisplayPort Cable with Latches (M/M) 50 ft. (15.24 m)

MODEL NUMBER: **P580-050**

**Highlights**

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI
- To achieve maximum performance, a signal booster such as the B121-000 must be used with this cable

Package Includes

DisplayPort Monitor Cable - 50ft

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Provides up to 1080p resolution
- Monitor Resolution Support: 2560x1600 at 60 Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)
- To achieve maximum performance, a signal booster such as the B121-000 must be used with this cable

Specifications

OVERVIEW	
UPC Code	037332176578
Product Type	Passive Cable
Technology	DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Latching or Gripping Connector	Yes
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 1.00
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 2.54
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.