

## DisplayPort to HDMI Adapter Cable (M/M), 6 ft. (1.8 m), TAA

MODEL NUMBER: **P582-006**



Connects a DisplayPort video/audio source device to an HDMI monitor, television or projector.

### Features

#### Connects Your Computer's DisplayPort Output to an HDMI Monitor or TV

This in-line passive adapter cable lets you connect a device with a DisplayPort connector with an HDMI monitor, television or projector. It supports high-definition resolutions up to 1920 x 1080 (1080p). **Note:** Because it is a passive adapter, the connected DisplayPort source device must have a DisplayPort++ (DP++) dual-mode port.

#### TAA-Compliant for GSA Schedule Purchases

The P582-006 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

OVERVIEW	
UPC Code	037332148049
Product Type	Passive Cable
Technology	HDMI; DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)

### Highlights

- Recommended for home theaters, digital signage, trade shows and classrooms
- Supports HD resolutions up to 1920 x 1080 (1080p)
- Passive adapter requires the connected source to support DisplayPort++ dual mode
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Source device with DisplayPort output (Blu-ray player, media server, laptop)
- Display device with HDMI input (HDTV, projector, monitor)
- Not for use with MST Hubs. For compatibility with MST Hubs, P582-006-V2 is recommended.

### Package Includes

P582-006 DisplayPort to HDMI Adapter Cable, M/M, 6 ft. (1.8 m)



*Powering Business Worldwide*

TRIPP LITE  
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.5mm
Wire Gauge (AWG)	28
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.