

USB Cable Kit for KVM Switch B006-VU4-R, 10 ft. (3.05 m)

MODEL NUMBER: **P758-010**



Description

This USB KVM cable kit connects a USB computer to a B006-VU4-R KVM switch. The KVM switch side of the cable kit consists of a USB-B Male cable and a SVGA (HD15) Female monitor cable. The computer side of the cable kit consists of a USB-A Male cable and a SVGA (HD15) Male monitor cable. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a USB computer to a B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable
- Molded ends with easy-grip textured overmold
- Supports any VGA/SVGA monitor
- Constructed of mini-coax (RGB) and paired video wire
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection

Specifications

OVERVIEW	
UPC Code	037332014993
Accessory Type	Cable Kit
Technology	VGA/SVGA
Accessory Class	KVM Switch Accessories
CONNECTIONS	

Highlights

- Required to connect a USB computer to the B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable

System Requirements

- A USB computer
- A USB KVM switch (model # B006-VU4-R).

Package Includes

- 10-ft. (3.05 m) USB Cable Kit for the B006-VU4-R KVM Switch



Powering Business Worldwide

TRIPP LITE
SERIES

KVM Switch Side 1	HD15 (Female)
KVM Switch Side 2	USB B (Male)
Computer Side 1	HD15 (Male)
Computer Side 2	USB A (Male)
PHYSICAL	
Color	Gray
Cable Jacket Color	Gray
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 1.27
Shipping Weight (lbs.)	0.85
Shipping Weight (kg)	0.39
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.