

Serial ATA (SATA) Latching Signal Cable (7Pin/7Pin), 12-in. (30.48 cm)

MODEL NUMBER: **P940-12I**



Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices
- Metal latches ensure secure connections
- Support data transfer rates of up to 6.0 Gbps
- Narrow cables design simplifies cable routing and installation and improves air flow within CPU (no more big ribbons blocking air movement)
- Meets Serial ATA 1.0 standards, including Errata 029
- Cable is shielded to protect against EMI/RFI

Specifications

OVERVIEW	
UPC Code	037332184382
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN SATA STRAIGHT (MALE)
Side B - Connector 1	7 PIN SATA STRAIGHT (MALE)
PHYSICAL	
Color	Red
Cable Jacket Color	Red
Cable Outer Diameter (OD)	2.4/8.0mm

Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI

Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

System Requirements

- Serial ATA device
- Serial ATA controller

Package Includes

- 12-in. Serial ATA (SATA) Latching Signal Cable 7Pin/7Pin, Straight/Straight



Powering Business Worldwide

TRIPP LITE
SERIES

Wire Gauge (AWG)	26
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Cable Length (cm)	30.48
Shipping Dimensions (hwd / in.)	0.12 x 4.00 x 6.00
Shipping Dimensions (hwd / cm)	0.32 x 10.16 x 15.24
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.125 x 4.000 x 6.000
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.