

1.5kW Single-Phase Local Metered PDU, 100-127V Outlets (14 5-15R), 5-15P, 15 ft. (4.57 m) Cord, 0U Vertical, 36 in.

MODEL NUMBER: PDUMV15-36



Highlights

- Local Metered single phase 12A 100-127V 0U 36in / 91cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug
- 14 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

Package Includes

- Local Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information

Features

- 12A single phase 100-127V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 100-127V input plug with 15-ft. (4.57 m) line cord
- 0U 36in / 91cm vertical rackmount format installs using no rack spaces
- 14 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW	
UPC Code	037332182869
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	100; 120; 125; 127
Recommended Electrical Service	Single-phase 15A 100-127V service
Maximum Input Amps	12
Maximum Input Amps Details	Agency de-rated to 12A continuous



Powering Business Worldwide

TRIPP LITE
SERIES

PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity; 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100-127V
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated safety cover
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Rack Height	0U
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	2.21 x 38.93 x 5.56
Shipping Dimensions (hwd / cm)	5.61 x 98.88 x 14.12
Shipping Weight (lbs.)	3.79
Shipping Weight (kg)	1.72
Unit Dimensions (hwd / in.)	36.000 x 1.750 x 1.250
Unit Dimensions (hwd / cm)	91.4 x 4.45 x 3.2
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)
Relative Humidity	5% to 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.