

4-Outlet Vertical Power Strip, 2-15A & 2-20A, 120V, 15 ft. (4.57 m) Cord, 5-20P, 12 in.

MODEL NUMBER: **PS120420**



The P120420 power strip provides horizontal or vertical power distribution for rackmount, raceway and workbench applications in a convenient 12-in. mountable housing.

Description

The PS120420 provides a 20-amp, 120v power strip with 2 standard NEMA 5-15 outlets and 2 NEMA 5-20R outlets in a rugged, all-metal, mountable housing. It allows for both vertical and horizontal mounting, making it ideal for a variety of uses including office, rackmount, workbench, industrial and telecom applications. With a NEMA 5-20P, 15-ft. (4.57 m) power cord, you don't have to install the PS120420 next to outlets you already have; it can be mounted across the room and deliver reliable service where you need it most. A lighted and covered On/Off switch helps prevent accidental shut-offs, while a 20-amp circuit breaker guards against dangerous circuit overloads. Its sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

Features

Multi-Outlet Power Distribution

Vertical or Horizontal Mounting

Extra Long Power Cord

Premium Safety Features

Heavy-Duty Housing

Highlights

- Ideal for applications needing multiple convenience outlets for powering a variety of electronic equipment
- 12-in. mountable housing with 2 NEMA 5-15R and 2 NEMA 5-20R outlets and a 15-ft. (4.57 m) power cord
- Lighted, covered On/Off switch and 20-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

Package Includes

- PS120420
- Mounting hardware
- Instruction manual

Specifications

OVERVIEW	
UPC Code	037332186126
INPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(2) 5-15R; (2) 5-20R
Circuit Breaker (amps)	20
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
Outlet Spacing	1.77 in center to center.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	1.77 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.70 x 6.00 x 15.70
Shipping Dimensions (hwd / cm)	9.40 x 15.24 x 39.88
Shipping Weight (lbs.)	3.60
Shipping Weight (kg)	1.63
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 12.000



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / cm)	4.21 x 6.34 x 15.6
Unit Weight (lbs.)	2.75
Unit Weight (kg)	1.25
Outlet Spacing	1.77 in.
Mounting Details	Includes mounting clips
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.