

## Power It! 4-Outlet Power Strip, 10 ft. (3.05 m) Cord

MODEL NUMBER: **PS410**



### Highlights

- 4 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 10-ft. (3.05 m) power cord
- ABS fire retardant plastic

### Package Includes

- PS410 power strip
- Warranty information
- Instruction manual

### Description

The Power It!® PS410 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes four NEMA 5-15R outlets and 10-foot (3.1-meter) AC power cord. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features ABS fire-retardant plastic case to stand up to the most demanding environments, illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 4 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 10-ft. (3.05 m) AC power cord
- ABS fire retardant plastic case provides extra safety and durability
- UL certification

### Specifications

OVERVIEW	
UPC Code	037332175540
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V

Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
<b>PHYSICAL</b>	
Color	Light Gray
Material of Construction	ABS, Fire Retardant
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	12.00 x 1.50 x 5.90
Shipping Dimensions (hwd / cm)	30.48 x 3.81 x 14.99
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
Unit Dimensions (hwd / in.)	1.210 x 1.850 x 8.110
Unit Dimensions (hwd / cm)	3 x 4.7 x 20.6
Unit Weight (lbs.)	1.4
Unit Weight (kg)	0.64



*Powering Business Worldwide*

TRIPP LITE  
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.