

## Safe-IT UL 1363 Medical-Grade Power Strip, 4 Hospital-Grade Outlets, USB Charging, Safety Covers, Antimicrobial, 15 ft. Cord

MODEL NUMBER: PS-415-HGUSB



Delivers power to medical equipment in areas outside patient care vicinities, including nursing stations, labs, offices and pharmacies.

### Features

#### Medical-Grade Power Strip Approved for Hospitals, Clinics and Other Medical Facilities

The PS-415-HGUSB features four NEMA 5-15R-HG hospital-grade outlets that supply power to equipment used in areas outside patient care vicinities, including nursing stations, pharmacies, office and administration areas, and labs. This power strip has a NEMA 5-15P-HG "green dot" plug and meets UL 1363 standards.

#### Dual USB Ports Provide Charging Power

One USB-A port and one USB-C Power Delivery (PD) port let you charge smartphones, tablets and other vital mobile devices. The USB-C PD port provides up to 30W.

#### Protective Coating Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ power strip is protected by an antimicrobial coating that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Premium Safety Features Help Ensure Proper Power Connections

With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Four locking plastic safety covers are included to block access to unused outlets.

#### Ready for Installation in Demanding Medical Environments

The 15-foot cord gives you some leeway in positioning the power strip away from a standard NEMA 5-15R wall outlet. Built-in mounting flanges let you mount the all-metal housing to a stable, flat surface.

#### Smart Information with Eaton EPAS

Scan the Easy Asset QR code on the side of the power strip to access product resources and other critical information.

### Highlights

- Medical-grade power strip approved for use outside patient care vicinities
- 4 NEMA 5-15R-HG outlets come with optional locking covers for protection
- Dual USB ports provide charging power to 2 mobile devices at the same time
- 15 ft. power cord allows flexibility in placing power strip away from wall outlet
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

### Package Includes

- PS-415-HGUSB UL 1363 Medical-Grade Power Strip, 4 Outlets, 15 ft. Cord
- (4) Outlet safety covers
- Owner's manual

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332287717
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
Switches	No power switch
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Watts	30
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB C Power Delivery
Charging Ports / Amps	2A; (1) 3A / 2A / 1.5A



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	Inner outlets = 1.27 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	10.16 x 5.98 x 2.36
Shipping Dimensions (hwd / cm)	25.81 x 15.19 x 5.99
Shipping Weight (lbs.)	2.79
Shipping Weight (kg)	1.27
Unit Dimensions (hwd / in.)	8.540 x 2.500 x 1.660
Unit Weight (lbs.)	2.56
Unit Weight (kg)	1.16
Mounting Details	Includes flanges
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); UL 1363; UL Listed; cUL Listed
Product Compliance	RoHS; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.