


24-Outlet Vertical Power Strip, 120V, 15A, 5-15P, 15 ft. (4.57 m) Cord, 72 in.

MODEL NUMBER: PS7224



Highlights

- 24 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15-ft. (4.57 m) cord
- 72" length

Package Includes

- PS7224
- Mounting hardware
- Instruction manual

Description

The PS7224 power strip offers 15A 120V multi-outlet AC power distribution in a convenient 72-inch mountable housing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications. Includes 24 NEMA 5-15R output receptacles with 2.8-inch center-to-center spacing, 15-foot (4.6-meter) AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

Features

- Sturdy all-metal 72 inch corded strip format with 2.795 inch center-to-center outlet spacing
- Included mounting hardware
- Includes 24 NEMA 5-15R output receptacles
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332011480
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120



Powering Business Worldwide

TRIPP LITE
SERIES

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(24) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(12) Yes
Right-Angle Outlets	No
Outlet Spacing	2.795 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
Housing Color	Silver
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	2.83 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.00 x 2.00 x 76.00
Shipping Dimensions (hwd / cm)	7.62 x 5.08 x 193.04
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
Unit Dimensions (hwd / in.)	1.500 x 1.500 x 72.000
Unit Dimensions (hwd / cm)	183 x 3.8 x 3.8
Unit Weight (lbs.)	5.5
Unit Weight (kg)	2.49



Powering Business Worldwide

TRIPP LITE
SERIES

Outlet Spacing	2.795 in.
Mounting Details	Includes mounting clips
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.