

## 4U UPS Replacement 192VDC Battery Cartridge (1 Set of 16) for Select SmartOnline UPS

MODEL NUMBER: **RBC5-192**



### Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

### Package Includes

- Set of 16 pre-wired batteries ready to install

### Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

Compatible with models SU5000RT4UHV, SU5000RT4UTF, SU6000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UTF, SU6000RT4UTFHW, SU6000RT4UHVPM and other UPS products specifying the use of this replacement battery cartridge

### Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

## Specifications

OVERVIEW	
UPC Code	037332154576
BATTERY	
DC System Voltage (VDC)	192
Included Battery Set	Contains (16) 12V 5.5AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	
Rack Height	4U



Powering Business Worldwide

TRIPP LITE  
SERIES

Minimum Required Rack Depth (cm)	22.86
Minimum Required Rack Depth (inches)	9
Shipping Dimensions (hwd / in.)	11.30 x 19.30 x 15.30
Shipping Dimensions (hwd / cm)	28.70 x 49.02 x 38.86
Shipping Weight (lbs.)	69.00
Shipping Weight (kg)	31.30
Unit Dimensions (hwd / in.)	8.350 x 7.090 x 5.510
Unit Dimensions (hwd / cm)	21.2 x 18 x 14
Unit Weight (lbs.)	63.9300
Unit Weight (kg)	29.00
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.