

Specifications



Eaton 010-0026

Eaton ePDU Cable, C19 input, 1.44 kW max, 100-240V, 10A, 8 ft cord, Single-phase, Outlets: Hardwired

General specifications

PRODUCT NAME	Eaton PDU cable
CATALOG NUMBER	010-0026
UPC	786685347738
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	8 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed

Product specifications

TYPE	ePDU Cable
OUTLET CONTROL	No
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
MOUNTING DIRECTION	Horizontal
COLOR	Black
INPUT CONNECTION	C19
CORD LENGTH	8 ft
WATTAGE	1.44 kW max
AMPERAGE RATING	32AA
INPUT VOLTAGE	100-240V
PHASE	Single-phase
FREQUENCY RATING	50-60 Hz
OUTLETS	Hardwired

Resources

BROCHURES

[Eaton rack PDU guide to plugs and receptacles](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 010-0026](#)

[Product Data Sheet - 010-0026](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

